

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773295

Luminaire Tested: LD6D85BD010-EU6DR7070959040-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR7070959040-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10981.5 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P773295

CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P773295

CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	947018
5°	944658
10°	942611
15°	942350
20°	933136
25°	876562
30°	781456
35°	623058
40°	413712
45°	247337
50°	128233
55°	67395
60°	23841
65°	414
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 247337 cd/sqm



TEST NUMBER: P773295

CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	819.1	7.5
10°-20°	2349.2	21.4
20°-30°	3314.0	30.2
30°-40°	2860.8	26.1
40°-50°	1281.1	11.7
50°-60°	335.4	3.1
60°-70°	21.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6482.3	59.0
0°-40°	9343.1	85.1
0°-60°	10959.6	99.8
0°-90°	10981.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10981.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8668	
5°	8613	819
15°	8331	2349
25°	7271	3314
35°	4671	2861
45°	1601	1281
55°	354	335
65°	2	22
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P773295

CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8667.5
2.5°	8658.2
5°	8613.0
7.5°	8575.6
10°	8496.1
12.5°	8424.4
15°	8330.9
17.5°	8223.3
20°	8025.4
22.5°	7699.6
25°	7271.0
27.5°	6773.8
30°	6194.0
32.5°	5484.8
35°	4671.2
37.5°	3773.4
40°	2900.6
42.5°	2203.9
45°	1600.7
47.5°	1103.5
50°	754.4
52.5°	520.6
55°	353.8
57.5°	213.5
60°	109.1
62.5°	34.3
65°	1.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)