

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774277

Luminaire Tested: LD6D95BD010-EU6DR3570959030-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10679.1 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774277

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P774277

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3210474
5°	3135039
10°	2825502
15°	2193041
20°	1243864
25°	483923
30°	180540
35°	98957
40°	64683
45°	39371
50°	25055
55°	17697
60°	12958
65°	7032
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 39371 cd/sqm



TEST NUMBER: P774277

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2628.9	24.6
10°-20°	5132.7	48.1
20°-30°	2093.3	19.6
30°-40°	501.0	4.7
40°-50°	208.8	2.0
50°-60°	86.4	0.8
60°-70°	27.0	0.3
70°-80°	0.6	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9854.9	92.3
0°-40°	10355.9	97.0
0°-60°	10651.0	99.7
0°-90°	10679.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10679.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	29384	
5°	28584	###
15°	19388	5133
25°	4014	2093
35°	742	501
45°	255	209
55°	93	86
65°	27	27
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774277

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	29383.6
2.5°	29207.3
5°	28584.0
7.5°	27340.5
10°	25467.3
12.5°	22829.7
15°	19387.7
17.5°	15178.1
20°	10697.8
22.5°	6821.5
25°	4014.1
27.5°	2269.0
30°	1431.0
32.5°	1004.7
35°	741.9
37.5°	573.7
40°	453.5
42.5°	349.3
45°	254.8
47.5°	190.7
50°	147.4
52.5°	117.0
55°	92.9
57.5°	75.3
60°	59.3
62.5°	43.3
65°	27.2
67.5°	9.6
70°	1.6
72.5°	1.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)