

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774359

Luminaire Tested: LD6D95BD010-EU6DR4070959030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4070959030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12286.0 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774359

CATALOG NUMBER: LD6D95BD010-EU6DR4070959030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P774359

CATALOG NUMBER: LD6D95BD010-EU6DR4070959030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3125404
5°	3110219
10°	2939832
15°	2499232
20°	1703409
25°	710737
30°	223473
35°	103865
40°	57437
45°	26330
50°	12782
55°	7010
60°	3649
65°	1293
70°	543
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26330 cd/sqm



TEST NUMBER: P774359

CATALOG NUMBER: LD6D95BD010-EU6DR4070959030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2647.9	21.6
10°-20°	5932.0	48.3
20°-30°	2969.4	24.2
30°-40°	544.3	4.4
40°-50°	150.2	1.2
50°-60°	35.3	0.3
60°-70°	6.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11549.3	94.0
0°-40°	12093.6	98.4
0°-60°	12279.0	99.9
0°-90°	12286.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12286.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	28605	
5°	28358	###
15°	22095	5932
25°	5896	2969
35°	779	544
45°	170	150
55°	37	35
65°	5	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774359

CATALOG NUMBER: LD6D95BD010-EU6DR4070959030-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	28605.0
2.5°	28563.3
5°	28357.7
7.5°	27702.7
10°	26497.8
12.5°	24619.6
15°	22094.6
17.5°	18811.0
20°	14650.1
22.5°	9987.9
25°	5895.5
27.5°	3116.5
30°	1771.3
32.5°	1144.7
35°	778.7
37.5°	556.5
40°	402.7
42.5°	275.7
45°	170.4
47.5°	108.6
50°	75.2
52.5°	53.5
55°	36.8
57.5°	23.4
60°	16.7
62.5°	10.0
65°	5.0
67.5°	3.3
70°	1.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)