

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774432

Luminaire Tested: LD6D95BD010-EU6DR4570959030-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774432
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4570959030-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10094.2 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774432

CATALOG NUMBER: LD6D95BD010-EU6DR4570959030-6LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P774432

CATALOG NUMBER: LD6D95BD010-EU6DR4570959030-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66		
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63		
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1949409
5°	1893900
10°	1811952
15°	1658323
20°	1315627
25°	821359
30°	452712
35°	203275
40°	80058
45°	37733
50°	17882
55°	9353
60°	4589
65°	1086
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37733 cd/sqm



TEST NUMBER: P774432

CATALOG NUMBER: LD6D95BD010-EU6DR4570959030-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1622.5	16.1
10°-20°	3993.1	39.6
20°-30°	3162.2	31.3
30°-40°	1053.0	10.4
40°-50°	209.0	2.1
50°-60°	47.5	0.5
60°-70°	6.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8777.7	87.0
0°-40°	9830.8	97.4
0°-60°	10087.2	99.9
0°-90°	10094.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10094.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17842	
5°	17268	###
15°	14660	3993
25°	6813	3162
35°	1524	1053
45°	244	209
55°	49	47
65°	4	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774432

CATALOG NUMBER: LD6D95BD010-EU6DR4570959030-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	17841.8
2.5°	17725.3
5°	17267.8
7.5°	16890.3
10°	16331.8
12.5°	15588.1
15°	14660.5
17.5°	13265.6
20°	11315.0
22.5°	8991.1
25°	6813.1
27.5°	4988.8
30°	3588.3
32.5°	2440.4
35°	1524.0
37.5°	903.7
40°	561.3
42.5°	369.1
45°	244.2
47.5°	157.2
50°	105.2
52.5°	70.2
55°	49.1
57.5°	32.3
60°	21.0
62.5°	11.2
65°	4.2
67.5°	1.4
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)