

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774436

Luminaire Tested: LD6D95BD010-EU6DR4570959030-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774436
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4570959030-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11288.5 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774436

CATALOG NUMBER: LD6D95BD010-EU6DR4570959030-6LBS1B

Luminous Intensity Polar Plot



TEST NUMBER: P774436

CATALOG NUMBER: LD6D95BD010-EU6DR4570959030-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66		
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63		
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2180047
5°	2117983
10°	2026334
15°	1854521
20°	1471282
25°	918540
30°	506269
35°	227324
40°	89529
45°	42199
50°	20007
55°	10458
60°	5135
65°	1215
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42199 cd/sqm



TEST NUMBER: P774436

CATALOG NUMBER: LD6D95BD010-EU6DR4570959030-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1814.4	16.1
10°-20°	4465.6	39.6
20°-30°	3536.3	31.3
30°-40°	1177.6	10.4
40°-50°	233.7	2.1
50°-60°	53.1	0.5
60°-70°	7.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9816.3	87.0
0°-40°	10993.9	97.4
0°-60°	11280.7	99.9
0°-90°	11288.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11288.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19953	
5°	19311	###
15°	16395	4466
25°	7619	3536
35°	1704	1178
45°	273	234
55°	55	53
65°	5	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774436

CATALOG NUMBER: LD6D95BD010-EU6DR4570959030-6LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	19952.7
2.5°	19822.5
5°	19310.9
7.5°	18888.7
10°	18264.1
12.5°	17432.3
15°	16395.0
17.5°	14835.1
20°	12653.7
22.5°	10054.8
25°	7619.2
27.5°	5579.0
30°	4012.8
32.5°	2729.1
35°	1704.3
37.5°	1010.7
40°	627.7
42.5°	412.7
45°	273.1
47.5°	175.8
50°	117.7
52.5°	78.5
55°	54.9
57.5°	36.1
60°	23.5
62.5°	12.6
65°	4.7
67.5°	1.6
70°	1.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)