

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774513

Luminaire Tested: LD6D95BD010-EU6DR5070959030-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5070959030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11031.2 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774513

CATALOG NUMBER: LD6D95BD010-EU6DR5070959030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774513

CATALOG NUMBER: LD6D95BD010-EU6DR5070959030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1942001
5°	1921637
10°	1889992
15°	1720989
20°	1432052
25°	1016551
30°	538062
35°	219268
40°	81427
45°	37285
50°	15281
55°	8001
60°	3933
65°	1163
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37285 cd/sqm



TEST NUMBER: P774513

CATALOG NUMBER: LD6D95BD010-EU6DR5070959030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1656.1	15.0
10°-20°	4185.2	37.9
20°-30°	3759.4	34.1
30°-40°	1177.1	10.7
40°-50°	206.1	1.9
50°-60°	41.1	0.4
60°-70°	6.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9600.7	87.0
0°-40°	10777.8	97.7
0°-60°	11025.0	99.9
0°-90°	11031.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11031.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17774	
5°	17521	###
15°	15214	4185
25°	8432	3759
35°	1644	1177
45°	241	206
55°	42	41
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774513

CATALOG NUMBER: LD6D95BD010-EU6DR5070959030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	17774.0
2.5°	17685.5
5°	17520.7
7.5°	17269.0
10°	17035.2
12.5°	16285.9
15°	15214.5
17.5°	13853.8
20°	12316.3
22.5°	10537.6
25°	8432.2
27.5°	6199.4
30°	4264.8
32.5°	2776.8
35°	1643.9
37.5°	944.1
40°	570.9
42.5°	371.6
45°	241.3
47.5°	146.9
50°	89.9
52.5°	61.4
55°	42.0
57.5°	28.5
60°	18.0
62.5°	10.5
65°	4.5
67.5°	1.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)