

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774595

Luminaire Tested: LD6D95BD010-EU6DR5570959030-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5570959030-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11434.5 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774595

CATALOG NUMBER: LD6D95BD010-EU6DR5570959030-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774595

CATALOG NUMBER: LD6D95BD010-EU6DR5570959030-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1400941
5°	1345301
10°	1340231
15°	1301728
20°	1167182
25°	964616
30°	728644
35°	528329
40°	338118
45°	154425
50°	50501
55°	21792
60°	9375
65°	1241
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 154425 cd/sqm



TEST NUMBER: P774595

CATALOG NUMBER: LD6D95BD010-EU6DR5570959030-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1167.2	10.2
10°-20°	3185.4	27.9
20°-30°	3630.1	31.7
30°-40°	2471.2	21.6
40°-50°	851.6	7.4
50°-60°	117.7	1.0
60°-70°	11.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7982.6	69.8
0°-40°	10453.8	91.4
0°-60°	11423.1	99.9
0°-90°	11434.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11434.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12822	
5°	12266	###
15°	11508	3185
25°	8001	3630
35°	3961	2471
45°	999	852
55°	114	118
65°	5	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774595

CATALOG NUMBER: LD6D95BD010-EU6DR5570959030-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	12822.0
2.5°	12528.0
5°	12265.9
7.5°	12137.2
10°	12080.0
12.5°	11889.3
15°	11508.0
17.5°	10902.6
20°	10038.3
22.5°	9040.5
25°	8001.4
27.5°	6919.4
30°	5775.4
32.5°	4806.3
35°	3961.0
37.5°	3157.0
40°	2370.6
42.5°	1642.9
45°	999.4
47.5°	538.6
50°	297.1
52.5°	176.4
55°	114.4
57.5°	73.1
60°	42.9
62.5°	19.1
65°	4.8
67.5°	1.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)