

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774252

Luminaire Tested: LD6D95BD010-EU6DR3570959024-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959024-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9608.3 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774252

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P774252

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96						
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88						
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84						
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81						
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78						
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75						
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72						
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70						
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2888570
5°	2820691
10°	2542190
15°	1973145
20°	1119138
25°	435400
30°	162435
35°	89033
40°	58193
45°	35416
50°	22539
55°	15925
60°	11647
65°	6334
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35416 cd/sqm



TEST NUMBER: P774252

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2365.3	24.6
10°-20°	4618.1	48.1
20°-30°	1883.4	19.6
30°-40°	450.7	4.7
40°-50°	187.8	2.0
50°-60°	77.7	0.8
60°-70°	24.3	0.3
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8866.8	92.3
0°-40°	9317.5	97.0
0°-60°	9583.1	99.7
0°-90°	9608.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9608.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26437	
5°	25718	###
15°	17444	4618
25°	3612	1883
35°	668	451
45°	229	188
55°	84	78
65°	24	24
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774252

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	26437.4
2.5°	26278.8
5°	25717.9
7.5°	24599.1
10°	22913.7
12.5°	20540.6
15°	17443.7
17.5°	13656.3
20°	9625.1
22.5°	6137.5
25°	3611.6
27.5°	2041.5
30°	1287.5
32.5°	904.0
35°	667.5
37.5°	516.1
40°	408.0
42.5°	314.3
45°	229.2
47.5°	171.6
50°	132.6
52.5°	105.2
55°	83.6
57.5°	67.8
60°	53.3
62.5°	38.9
65°	24.5
67.5°	8.7
70°	1.4
72.5°	1.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)