

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774672

Luminaire Tested: LD6D95BD010-EU6DR6070959030-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959030-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12392.4 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774672

CATALOG NUMBER: LD6D95BD010-EU6DR6070959030-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P774672

CATALOG NUMBER: LD6D95BD010-EU6DR6070959030-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1354997
5°	1351695
10°	1396592
15°	1398023
20°	1286338
25°	1094117
30°	833675
35°	589552
40°	346191
45°	139684
50°	46642
55°	22440
60°	9222
65°	1370
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 139684 cd/sqm



TEST NUMBER: P774672

CATALOG NUMBER: LD6D95BD010-EU6DR6070959030-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1188.9	9.6
10°-20°	3424.0	27.6
20°-30°	4098.0	33.1
30°-40°	2741.0	22.1
40°-50°	812.6	6.6
50°-60°	116.8	0.9
60°-70°	11.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8710.9	70.3
0°-40°	11451.8	92.4
0°-60°	12381.3	99.9
0°-90°	12392.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12392.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12402	
5°	12324	###
15°	12359	3424
25°	9076	4098
35°	4420	2741
45°	904	813
55°	118	117
65°	5	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774672

CATALOG NUMBER: LD6D95BD010-EU6DR6070959030-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	12401.5
2.5°	12385.7
5°	12324.2
7.5°	12491.2
10°	12588.0
12.5°	12570.4
15°	12359.3
17.5°	11861.6
20°	11063.1
22.5°	10104.5
25°	9075.6
27.5°	7916.5
30°	6607.9
32.5°	5440.1
35°	4420.0
37.5°	3398.1
40°	2427.2
42.5°	1600.5
45°	904.0
47.5°	462.6
50°	274.4
52.5°	177.6
55°	117.8
57.5°	75.6
60°	42.2
62.5°	17.6
65°	5.3
67.5°	1.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)