

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774335

Luminaire Tested: LD6D95BD010-EU6DR4070959024-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4070959024-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10001.1 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774335

CATALOG NUMBER: LD6D95BD010-EU6DR4070959024-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774335

CATALOG NUMBER: LD6D95BD010-EU6DR4070959024-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	97
2	110	106	103	100		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		104	100	96	93		97	94	92		95	93	90		93	91	89
4	102	97	92	89		101	95	91	88		93	90	87		92	89	86		90	87	85
5	99	92	88	84		97	91	87	84		90	86	83		88	85	83		87	84	82
6	95	88	84	80		94	88	83	80		86	82	80		85	82	79		84	81	79
7	92	85	80	77		91	84	80	77		83	79	76		82	79	76		81	78	76
8	89	82	77	74		88	81	77	74		80	76	73		79	76	73		78	75	73
9	86	79	74	71		85	78	74	71		77	73	71		76	73	70		76	72	70
10	83	76	71	68		82	75	71	68		75	71	68		74	70	68		73	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2544169
5°	2531810
10°	2393111
15°	2034442
20°	1386624
25°	578560
30°	181915
35°	84551
40°	46754
45°	21432
50°	10403
55°	5696
60°	2972
65°	1060
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21432 cd/sqm



TEST NUMBER: P774335

CATALOG NUMBER: LD6D95BD010-EU6DR4070959024-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2155.5	21.6
10°-20°	4828.8	48.3
20°-30°	2417.1	24.2
30°-40°	443.1	4.4
40°-50°	122.2	1.2
50°-60°	28.7	0.3
60°-70°	5.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9401.4	94.0
0°-40°	9844.5	98.4
0°-60°	9995.4	99.9
0°-90°	10001.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10001.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23285	
5°	23084	###
15°	17986	4829
25°	4799	2417
35°	634	443
45°	139	122
55°	30	29
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774335

CATALOG NUMBER: LD6D95BD010-EU6DR4070959024-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	23285.3
2.5°	23251.3
5°	23084.0
7.5°	22550.7
10°	21570.0
12.5°	20041.0
15°	17985.6
17.5°	15312.7
20°	11925.6
22.5°	8130.4
25°	4799.1
27.5°	2536.9
30°	1441.9
32.5°	931.8
35°	633.9
37.5°	453.0
40°	327.8
42.5°	224.4
45°	138.7
47.5°	88.4
50°	61.2
52.5°	43.5
55°	29.9
57.5°	19.0
60°	13.6
62.5°	8.2
65°	4.1
67.5°	2.7
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)