

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774294

Luminaire Tested: LD6D95BD010-EU6DR3570959035-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774294
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959035-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11359.6 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774294

CATALOG NUMBER: LD6D95BD010-EU6DR3570959035-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P774294

CATALOG NUMBER: LD6D95BD010-EU6DR3570959035-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3415043
5°	3334796
10°	3005535
15°	2332772
20°	1323115
25°	514750
30°	192033
35°	105266
40°	68805
45°	41874
50°	26653
55°	18839
60°	13789
65°	7497
70°	543
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41874 cd/sqm



TEST NUMBER: P774294

CATALOG NUMBER: LD6D95BD010-EU6DR3570959035-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2796.4	24.6
10°-20°	5459.8	48.1
20°-30°	2226.7	19.6
30°-40°	532.9	4.7
40°-50°	222.1	2.0
50°-60°	91.9	0.8
60°-70°	28.8	0.3
70°-80°	0.7	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10482.9	92.3
0°-40°	11015.7	97.0
0°-60°	11329.7	99.7
0°-90°	11359.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11359.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	31256	
5°	30405	###
15°	20623	5460
25°	4270	2227
35°	789	533
45°	271	222
55°	99	92
65°	29	29
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774294

CATALOG NUMBER: LD6D95BD010-EU6DR3570959035-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	31255.9
2.5°	31068.4
5°	30405.3
7.5°	29082.6
10°	27090.0
12.5°	24284.4
15°	20623.0
17.5°	16145.3
20°	11379.4
22.5°	7256.2
25°	4269.8
27.5°	2413.6
30°	1522.1
32.5°	1068.7
35°	789.2
37.5°	610.2
40°	482.4
42.5°	371.6
45°	271.0
47.5°	202.8
50°	156.8
52.5°	124.4
55°	98.9
57.5°	80.1
60°	63.1
62.5°	46.0
65°	29.0
67.5°	10.2
70°	1.7
72.5°	1.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)