

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774114

Luminaire Tested: LD6D95BD010-EU6DR2570959027-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR2570959027-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9697.5 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774114

CATALOG NUMBER: LD6D95BD010-EU6DR2570959027-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774114

CATALOG NUMBER: LD6D95BD010-EU6DR2570959027-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82		
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79		
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4018698
5°	3742908
10°	2669922
15°	1572480
20°	978425
25°	536956
30°	245565
35°	92994
40°	42119
45°	25326
50°	10505
55°	6781
60°	4720
65°	3206
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25326 cd/sqm



TEST NUMBER: P774114

CATALOG NUMBER: LD6D95BD010-EU6DR2570959027-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2932.9	30.2
10°-20°	3972.4	41.0
20°-30°	2102.1	21.7
30°-40°	518.9	5.4
40°-50°	126.6	1.3
50°-60°	33.3	0.3
60°-70°	11.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9007.4	92.9
0°-40°	9526.3	98.2
0°-60°	9686.2	99.9
0°-90°	9697.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9697.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	36781	
5°	34126	###
15°	13902	3972
25°	4454	2102
35°	697	519
45°	164	127
55°	36	33
65°	12	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774114

CATALOG NUMBER: LD6D95BD010-EU6DR2570959027-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	36780.8
2.5°	36176.3
5°	34126.3
7.5°	30007.8
10°	24065.0
12.5°	18191.7
15°	13901.6
17.5°	10834.3
20°	8414.9
22.5°	6310.8
25°	4454.0
27.5°	2986.9
30°	1946.4
32.5°	1184.2
35°	697.2
37.5°	426.7
40°	295.3
42.5°	225.7
45°	163.9
47.5°	98.9
50°	61.8
52.5°	44.8
55°	35.6
57.5°	27.8
60°	21.6
62.5°	17.0
65°	12.4
67.5°	4.6
70°	1.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)