

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774368

Luminaire Tested: LD6D95BD010-EU6DR4070959035-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4070959035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11794.6 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774368

CATALOG NUMBER: LD6D95BD010-EU6DR4070959035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P774368

CATALOG NUMBER: LD6D95BD010-EU6DR4070959035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3000410
5°	2985833
10°	2822263
15°	2399283
20°	1635285
25°	682310
30°	214541
35°	99717
40°	55141
45°	25279
50°	12273
55°	6724
60°	3496
65°	1241
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25279 cd/sqm



TEST NUMBER: P774368

CATALOG NUMBER: LD6D95BD010-EU6DR4070959035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2542.0	21.6
10°-20°	5694.8	48.3
20°-30°	2850.6	24.2
30°-40°	522.6	4.4
40°-50°	144.2	1.2
50°-60°	33.9	0.3
60°-70°	6.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11087.4	94.0
0°-40°	11609.9	98.4
0°-60°	11788.0	99.9
0°-90°	11794.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11794.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27461	
5°	27224	###
15°	21211	5695
25°	5660	2851
35°	748	523
45°	164	144
55°	35	34
65°	5	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774368

CATALOG NUMBER: LD6D95BD010-EU6DR4070959035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	27461.0
2.5°	27420.9
5°	27223.6
7.5°	26594.7
10°	25438.1
12.5°	23635.0
15°	21211.0
17.5°	18058.7
20°	14064.2
22.5°	9588.4
25°	5659.7
27.5°	2991.9
30°	1700.5
32.5°	1098.9
35°	747.6
37.5°	534.2
40°	386.6
42.5°	264.7
45°	163.6
47.5°	104.3
50°	72.2
52.5°	51.3
55°	35.3
57.5°	22.5
60°	16.0
62.5°	9.6
65°	4.8
67.5°	3.2
70°	1.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)