

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774370

Luminaire Tested: LD6D95BD010-EU6DR4070959035-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4070959035-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11190.1 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774370

CATALOG NUMBER: LD6D95BD010-EU6DR4070959035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774370

CATALOG NUMBER: LD6D95BD010-EU6DR4070959035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2846636
5°	2832810
10°	2677622
15°	2276316
20°	1551475
25°	647337
30°	203539
35°	94608
40°	52317
45°	23981
50°	11644
55°	6381
60°	3322
65°	1189
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23981 cd/sqm



TEST NUMBER: P774370

CATALOG NUMBER: LD6D95BD010-EU6DR4070959035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2411.7	21.6
10°-20°	5402.9	48.3
20°-30°	2704.5	24.2
30°-40°	495.8	4.4
40°-50°	136.8	1.2
50°-60°	32.1	0.3
60°-70°	6.1	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10519.1	94.0
0°-40°	11014.9	98.4
0°-60°	11183.8	99.9
0°-90°	11190.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11190.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26054	
5°	25828	###
15°	20124	5403
25°	5370	2705
35°	709	496
45°	155	137
55°	34	32
65°	5	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774370

CATALOG NUMBER: LD6D95BD010-EU6DR4070959035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	26053.6
2.5°	26015.6
5°	25828.4
7.5°	25231.8
10°	24134.4
12.5°	22423.7
15°	20123.9
17.5°	17133.2
20°	13343.4
22.5°	9097.0
25°	5369.6
27.5°	2838.5
30°	1613.3
32.5°	1042.6
35°	709.3
37.5°	506.8
40°	366.8
42.5°	251.1
45°	155.2
47.5°	98.9
50°	68.5
52.5°	48.7
55°	33.5
57.5°	21.3
60°	15.2
62.5°	9.1
65°	4.6
67.5°	3.0
70°	1.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)