

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774446

Luminaire Tested: LD6D95BD010-EU6DR4570959035-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4570959035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11571.7 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774446

CATALOG NUMBER: LD6D95BD010-EU6DR4570959035-6LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P774446

CATALOG NUMBER: LD6D95BD010-EU6DR4570959035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2234743
5°	2171122
10°	2077169
15°	1901046
20°	1508187
25°	941590
30°	518973
35°	233033
40°	91782
45°	43250
50°	20517
55°	10725
60°	5266
65°	1241
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43250 cd/sqm



TEST NUMBER: P774446

CATALOG NUMBER: LD6D95BD010-EU6DR4570959035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1860.0	16.1
10°-20°	4577.6	39.6
20°-30°	3625.0	31.3
30°-40°	1207.2	10.4
40°-50°	239.6	2.1
50°-60°	54.4	0.5
60°-70°	7.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10062.5	87.0
0°-40°	11269.7	97.4
0°-60°	11563.7	99.9
0°-90°	11571.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11571.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20453	
5°	19795	###
15°	16806	4578
25°	7810	3625
35°	1747	1207
45°	280	240
55°	56	54
65°	5	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774446

CATALOG NUMBER: LD6D95BD010-EU6DR4570959035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	20453.3
2.5°	20319.8
5°	19795.4
7.5°	19362.6
10°	18722.3
12.5°	17869.7
15°	16806.3
17.5°	15207.3
20°	12971.1
22.5°	10307.1
25°	7810.4
27.5°	5719.0
30°	4113.5
32.5°	2797.6
35°	1747.1
37.5°	1036.0
40°	643.5
42.5°	423.1
45°	279.9
47.5°	180.2
50°	120.7
52.5°	80.4
55°	56.3
57.5°	37.0
60°	24.1
62.5°	12.9
65°	4.8
67.5°	1.6
70°	1.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)