

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774526

Luminaire Tested: LD6D95BD010-EU6DR5070959035-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5070959035-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11147.4 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774526

CATALOG NUMBER: LD6D95BD010-EU6DR5070959035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774526

CATALOG NUMBER: LD6D95BD010-EU6DR5070959035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			98
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			95
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			91
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			87
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			83
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			79
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			76
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			73
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			70
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1962454
5°	1941884
10°	1909896
15°	1739110
20°	1447144
25°	1027257
30°	543727
35°	221575
40°	82297
45°	37671
50°	15451
55°	8077
60°	3977
65°	1163
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37671 cd/sqm



TEST NUMBER: P774526

CATALOG NUMBER: LD6D95BD010-EU6DR5070959035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1673.5	15.0
10°-20°	4229.3	37.9
20°-30°	3799.0	34.1
30°-40°	1189.5	10.7
40°-50°	208.3	1.9
50°-60°	41.5	0.4
60°-70°	6.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9701.8	87.0
0°-40°	10891.3	97.7
0°-60°	11141.1	99.9
0°-90°	11147.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11147.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17961	
5°	17705	###
15°	15375	4229
25°	8521	3799
35°	1661	1189
45°	244	208
55°	42	42
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774526

CATALOG NUMBER: LD6D95BD010-EU6DR5070959035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	17961.2
2.5°	17871.8
5°	17705.3
7.5°	17450.9
10°	17214.6
12.5°	16457.5
15°	15374.7
17.5°	13999.8
20°	12446.1
22.5°	10648.6
25°	8521.0
27.5°	6264.7
30°	4309.7
32.5°	2806.0
35°	1661.2
37.5°	954.0
40°	577.0
42.5°	375.5
45°	243.8
47.5°	148.4
50°	90.9
52.5°	62.1
55°	42.4
57.5°	28.8
60°	18.2
62.5°	10.6
65°	4.5
67.5°	1.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)