

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774266

Luminaire Tested: LD6D95BD010-EU6DR3570959027-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9720.5 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774266

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774266

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2922255
5°	2853594
10°	2571846
15°	1996164
20°	1132195
25°	440475
30°	164328
35°	90073
40°	58878
45°	35833
50°	22811
55°	16115
60°	11800
65°	6412
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35833 cd/sqm



TEST NUMBER: P774266

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2392.9	24.6
10°-20°	4671.9	48.1
20°-30°	1905.4	19.6
30°-40°	456.0	4.7
40°-50°	190.0	2.0
50°-60°	78.7	0.8
60°-70°	24.6	0.3
70°-80°	0.6	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8970.2	92.3
0°-40°	9426.2	97.0
0°-60°	9694.9	99.7
0°-90°	9720.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9720.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26746	
5°	26018	###
15°	17647	4672
25°	3654	1905
35°	675	456
45°	232	190
55°	85	79
65°	25	25
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774266

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	26745.7
2.5°	26585.3
5°	26017.9
7.5°	24886.0
10°	23181.0
12.5°	20780.2
15°	17647.2
17.5°	13815.5
20°	9737.4
22.5°	6209.1
25°	3653.7
27.5°	2065.3
30°	1302.5
32.5°	914.5
35°	675.3
37.5°	522.2
40°	412.8
42.5°	318.0
45°	231.9
47.5°	173.6
50°	134.2
52.5°	106.5
55°	84.6
57.5°	68.6
60°	54.0
62.5°	39.4
65°	24.8
67.5°	8.8
70°	1.5
72.5°	1.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)