

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774341

Luminaire Tested: LD6D95BD010-EU6DR4070959027-6LBDP1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P774341  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D95BD010-EU6DR4070959027-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10096.7 lumens  
Efficiency: N/A  
Efficacy: 101.8 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P774341

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1B

### Luminous Intensity Polar Plot



TEST NUMBER: P774341

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 |  | 103 | 101 | 100 |  | 99  |
| 2   | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 99  | 102 | 99  | 97  |  | 99  | 97  | 95  |  | 96  |
| 3   | 106 | 101 | 97  | 94  | 104 | 100 | 96  | 93  | 97  | 94  | 92  |  | 95  | 93  | 90  |  | 93  |
| 4   | 102 | 97  | 92  | 89  | 101 | 95  | 91  | 88  | 93  | 90  | 87  |  | 92  | 89  | 86  |  | 90  |
| 5   | 99  | 92  | 88  | 84  | 97  | 91  | 87  | 84  | 90  | 86  | 83  |  | 88  | 85  | 83  |  | 87  |
| 6   | 95  | 88  | 84  | 80  | 94  | 88  | 83  | 80  | 86  | 82  | 80  |  | 85  | 82  | 79  |  | 84  |
| 7   | 92  | 85  | 80  | 77  | 91  | 84  | 80  | 77  | 83  | 79  | 76  |  | 82  | 79  | 76  |  | 81  |
| 8   | 89  | 82  | 77  | 74  | 88  | 81  | 77  | 74  | 80  | 76  | 73  |  | 79  | 76  | 73  |  | 78  |
| 9   | 86  | 79  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  |  | 76  | 73  | 70  |  | 76  |
| 10  | 83  | 76  | 71  | 68  | 82  | 75  | 71  | 68  | 75  | 71  | 68  |  | 74  | 70  | 68  |  | 73  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2568480 |
| 5°  | 2555994 |
| 10° | 2415977 |
| 15° | 2053887 |
| 20° | 1399867 |
| 25° | 584081  |
| 30° | 183656  |
| 35° | 85352   |
| 40° | 47210   |
| 45° | 21648   |
| 50° | 10505   |
| 55° | 5753    |
| 60° | 2994    |
| 65° | 1060    |
| 70° | 447     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21648 cd/sqm

TEST NUMBER: P774341

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1B

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 2176.1  | 21.6      |
| 10°-20°   | 4875.0  | 48.3      |
| 20°-30°   | 2440.2  | 24.2      |
| 30°-40°   | 447.3   | 4.4       |
| 40°-50°   | 123.4   | 1.2       |
| 50°-60°   | 29.0    | 0.3       |
| 60°-70°   | 5.5     | 0.1       |
| 70°-80°   | 0.2     | 0.0       |
| 80°-90°   | 0.0     | 0.0       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-30°    | 9491.2  | 94.0      |
| 0°-40°    | 9938.6  | 98.4      |
| 0°-60°    | 10091.0 | 99.9      |
| 0°-90°    | 10096.7 | 100.0     |
| 90°-120°  | 0.0     | 0.0       |
| 90°-150°  | 0.0     | 0.0       |
| 90°-180°  | 0.0     | 0.0       |
| 0°-180°   | 10096.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 23508 |      |
| 5°  | 23304 | ###  |
| 15° | 18158 | 4875 |
| 25° | 4845  | 2440 |
| 35° | 640   | 447  |
| 45° | 140   | 123  |
| 55° | 30    | 29   |
| 65° | 4     | 6    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P774341

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 23507.8 |
| 2.5°  | 23473.5 |
| 5°    | 23304.5 |
| 7.5°  | 22766.2 |
| 10°   | 21776.1 |
| 12.5° | 20232.5 |
| 15°   | 18157.5 |
| 17.5° | 15459.0 |
| 20°   | 12039.5 |
| 22.5° | 8208.1  |
| 25°   | 4844.9  |
| 27.5° | 2561.2  |
| 30°   | 1455.7  |
| 32.5° | 940.7   |
| 35°   | 639.9   |
| 37.5° | 457.3   |
| 40°   | 331.0   |
| 42.5° | 226.6   |
| 45°   | 140.1   |
| 47.5° | 89.3    |
| 50°   | 61.8    |
| 52.5° | 43.9    |
| 55°   | 30.2    |
| 57.5° | 19.2    |
| 60°   | 13.7    |
| 62.5° | 8.2     |
| 65°   | 4.1     |
| 67.5° | 2.7     |
| 70°   | 1.4     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)