

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774342

Luminaire Tested: LD6D95BD010-EU6DR4070959027-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774342
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4070959027-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11329.3 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774342

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P774342

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96						
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88						
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84						
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81						
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77						
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74						
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72						
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69						
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2882047
5°	2868039
10°	2710917
15°	2304629
20°	1570765
25°	655390
30°	206075
35°	95782
40°	52973
45°	24290
50°	11780
55°	6458
60°	3365
65°	1189
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24290 cd/sqm



TEST NUMBER: P774342

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2441.7	21.6
10°-20°	5470.1	48.3
20°-30°	2738.1	24.2
30°-40°	501.9	4.4
40°-50°	138.5	1.2
50°-60°	32.5	0.3
60°-70°	6.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10649.9	94.0
0°-40°	11151.9	98.4
0°-60°	11322.9	99.9
0°-90°	11329.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11329.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26378	
5°	26150	###
15°	20374	5470
25°	5436	2738
35°	718	502
45°	157	139
55°	34	33
65°	5	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774342

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	26377.7
2.5°	26339.1
5°	26149.6
7.5°	25545.6
10°	24434.5
12.5°	22702.5
15°	20374.2
17.5°	17346.3
20°	13509.3
22.5°	9210.1
25°	5436.4
27.5°	2873.8
30°	1633.4
32.5°	1055.5
35°	718.1
37.5°	513.1
40°	371.4
42.5°	254.3
45°	157.2
47.5°	100.2
50°	69.3
52.5°	49.3
55°	33.9
57.5°	21.6
60°	15.4
62.5°	9.2
65°	4.6
67.5°	3.1
70°	1.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)