

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774497

Luminaire Tested: LD6D95BD010-EU6DR5070959027-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5070959027-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10038.8 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774497

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P774497

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1767304
5°	1748774
10°	1719978
15°	1566168
20°	1303233
25°	925098
30°	489653
35°	199541
40°	74110
45°	33932
50°	13904
55°	7277
60°	3584
65°	1060
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33932 cd/sqm



TEST NUMBER: P774497

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBPD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1507.1	15.0
10°-20°	3808.7	37.9
20°-30°	3421.2	34.1
30°-40°	1071.2	10.7
40°-50°	187.6	1.9
50°-60°	37.4	0.4
60°-70°	5.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8737.0	87.0
0°-40°	9808.2	97.7
0°-60°	10033.2	99.9
0°-90°	10038.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10038.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16175	
5°	15945	###
15°	13846	3809
25°	7674	3421
35°	1496	1071
45°	220	188
55°	38	37
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774497

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	16175.1
2.5°	16094.6
5°	15944.6
7.5°	15715.5
10°	15502.8
12.5°	14820.9
15°	13845.8
17.5°	12607.6
20°	11208.4
22.5°	9589.7
25°	7673.6
27.5°	5641.7
30°	3881.1
32.5°	2527.0
35°	1496.0
37.5°	859.1
40°	519.6
42.5°	338.2
45°	219.6
47.5°	133.6
50°	81.8
52.5°	55.9
55°	38.2
57.5°	25.9
60°	16.4
62.5°	9.5
65°	4.1
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)