

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774841

Luminaire Tested: LD6D95BD010-EU6DR7070959035-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774841
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR7070959035-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12605.1 lumens
Efficiency: N/A
Efficacy: 127.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774841

CATALOG NUMBER: LD6D95BD010-EU6DR7070959035-6LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P774841

CATALOG NUMBER: LD6D95BD010-EU6DR7070959035-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1087035
5°	1084322
10°	1081970
15°	1081674
20°	1071094
25°	1006160
30°	896997
35°	715172
40°	474886
45°	283911
50°	147185
55°	77358
60°	27359
65°	465
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 283911 cd/sqm



TEST NUMBER: P774841

CATALOG NUMBER: LD6D95BD010-EU6DR7070959035-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	940.2	7.5
10°-20°	2696.5	21.4
20°-30°	3804.0	30.2
30°-40°	3283.8	26.1
40°-50°	1470.6	11.7
50°-60°	385.0	3.1
60°-70°	25.1	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7440.6	59.0
0°-40°	10724.4	85.1
0°-60°	12580.0	99.8
0°-90°	12605.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12605.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9949	
5°	9886	940
15°	9563	2696
25°	8346	3804
35°	5362	3284
45°	1837	1471
55°	406	385
65°	2	25
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774841

CATALOG NUMBER: LD6D95BD010-EU6DR7070959035-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	9949.0
2.5°	9938.3
5°	9886.4
7.5°	9843.5
10°	9752.2
12.5°	9669.9
15°	9562.6
17.5°	9439.1
20°	9211.9
22.5°	8838.0
25°	8346.0
27.5°	7775.3
30°	7109.8
32.5°	6295.7
35°	5361.8
37.5°	4331.3
40°	3329.5
42.5°	2529.7
45°	1837.4
47.5°	1266.7
50°	865.9
52.5°	597.5
55°	406.1
57.5°	245.1
60°	125.2
62.5°	39.4
65°	1.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)