

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774658

Luminaire Tested: LD6D95BD010-EU6DR6070959027-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959027-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11456.1 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774658

CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P774658

CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1252620
5°	1249563
10°	1291071
15°	1292396
20°	1189146
25°	1011452
30°	770695
35°	545002
40°	320033
45°	129131
50°	43107
55°	20744
60°	8522
65°	1267
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 129131 cd/sqm



TEST NUMBER: P774658

CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1099.0	9.6
10°-20°	3165.3	27.6
20°-30°	3788.4	33.1
30°-40°	2533.8	22.1
40°-50°	751.2	6.6
50°-60°	108.0	0.9
60°-70°	10.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8052.7	70.3
0°-40°	10586.6	92.4
0°-60°	11445.8	99.9
0°-90°	11456.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11456.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11464	
5°	11393	###
15°	11426	3165
25°	8390	3788
35°	4086	2534
45°	836	751
55°	109	108
65°	5	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774658

CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	11464.5
2.5°	11449.9
5°	11393.0
7.5°	11547.5
10°	11636.9
12.5°	11620.6
15°	11425.5
17.5°	10965.4
20°	10227.2
22.5°	9341.1
25°	8389.9
27.5°	7318.4
30°	6108.7
32.5°	5029.0
35°	4086.0
37.5°	3141.3
40°	2243.8
42.5°	1479.6
45°	835.7
47.5°	427.6
50°	253.6
52.5°	164.2
55°	108.9
57.5°	69.9
60°	39.0
62.5°	16.3
65°	4.9
67.5°	1.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)