

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774149

Luminaire Tested: LD6D95BD010-EU6DR2570959040-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR2570959040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9357.7 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774149

CATALOG NUMBER: LD6D95BD010-EU6DR2570959040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774149

CATALOG NUMBER: LD6D95BD010-EU6DR2570959040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3877850
5°	3611733
10°	2576350
15°	1517371
20°	944124
25°	518137
30°	236960
35°	89740
40°	40635
45°	24429
50°	10148
55°	6534
60°	4567
65°	3077
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24429 cd/sqm



TEST NUMBER: P774149

CATALOG NUMBER: LD6D95BD010-EU6DR2570959040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2830.1	30.2
10°-20°	3833.2	41.0
20°-30°	2028.4	21.7
30°-40°	500.7	5.4
40°-50°	122.2	1.3
50°-60°	32.2	0.3
60°-70°	10.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8691.7	92.9
0°-40°	9192.4	98.2
0°-60°	9346.7	99.9
0°-90°	9357.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9357.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	35492	
5°	32930	###
15°	13414	3833
25°	4298	2028
35°	673	501
45°	158	122
55°	34	32
65°	12	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774149

CATALOG NUMBER: LD6D95BD010-EU6DR2570959040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	35491.7
2.5°	34908.4
5°	32930.3
7.5°	28956.1
10°	23221.6
12.5°	17554.2
15°	13414.4
17.5°	10454.6
20°	8119.9
22.5°	6089.6
25°	4297.9
27.5°	2882.2
30°	1878.2
32.5°	1142.7
35°	672.8
37.5°	411.7
40°	284.9
42.5°	217.8
45°	158.1
47.5°	95.5
50°	59.7
52.5°	43.3
55°	34.3
57.5°	26.9
60°	20.9
62.5°	16.4
65°	11.9
67.5°	4.5
70°	1.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)