

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774304

Luminaire Tested: LD6D95BD010-EU6DR3570959040-6LBDP1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P774304  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D95BD010-EU6DR3570959040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11861.0 lumens  
Efficiency: N/A  
Efficacy: 119.6 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P774304

CATALOG NUMBER: LD6D95BD010-EU6DR3570959040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P774304

CATALOG NUMBER: LD6D95BD010-EU6DR3570959040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 115 | 112 | 110 | 108 |  | 112 | 110 | 108 | 107 |  | 106 | 105 | 103 |  | 103 | 101 | 100 |  | 99  | 98  | 98  |
| 2   | 110 | 106 | 103 | 101 |  | 108 | 105 | 102 | 99  |  | 102 | 99  | 97  |  | 99  | 97  | 95  |  | 96  | 95  | 93  |
| 3   | 106 | 101 | 97  | 94  |  | 105 | 100 | 96  | 93  |  | 97  | 95  | 92  |  | 95  | 93  | 91  |  | 93  | 91  | 89  |
| 4   | 103 | 97  | 92  | 89  |  | 101 | 96  | 92  | 89  |  | 94  | 90  | 88  |  | 92  | 89  | 87  |  | 90  | 88  | 86  |
| 5   | 99  | 93  | 88  | 85  |  | 98  | 92  | 87  | 84  |  | 90  | 86  | 84  |  | 89  | 85  | 83  |  | 87  | 84  | 82  |
| 6   | 96  | 89  | 84  | 81  |  | 94  | 88  | 84  | 81  |  | 87  | 83  | 80  |  | 85  | 82  | 80  |  | 84  | 81  | 79  |
| 7   | 93  | 85  | 81  | 78  |  | 91  | 85  | 80  | 77  |  | 84  | 80  | 77  |  | 83  | 79  | 77  |  | 82  | 79  | 76  |
| 8   | 90  | 82  | 78  | 74  |  | 88  | 82  | 77  | 74  |  | 81  | 77  | 74  |  | 80  | 76  | 74  |  | 79  | 76  | 73  |
| 9   | 87  | 79  | 75  | 72  |  | 86  | 79  | 75  | 72  |  | 78  | 74  | 71  |  | 77  | 74  | 71  |  | 77  | 73  | 71  |
| 10  | 84  | 77  | 72  | 69  |  | 83  | 76  | 72  | 69  |  | 76  | 72  | 69  |  | 75  | 71  | 69  |  | 74  | 71  | 69  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 3565757 |
| 5°  | 3481973 |
| 10° | 3138182 |
| 15° | 2435729 |
| 20° | 1381508 |
| 25° | 537474  |
| 30° | 200512  |
| 35° | 109907  |
| 40° | 71843   |
| 45° | 43729   |
| 50° | 27826   |
| 55° | 19659   |
| 60° | 14401   |
| 65° | 7834    |
| 70° | 575     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43729 cd/sqm



TEST NUMBER: P774304

CATALOG NUMBER: LD6D95BD010-EU6DR3570959040-6LBDP1LI

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 2919.8  | 24.6      |
| 10°-20°   | 5700.7  | 48.1      |
| 20°-30°   | 2325.0  | 19.6      |
| 30°-40°   | 556.4   | 4.7       |
| 40°-50°   | 231.9   | 2.0       |
| 50°-60°   | 96.0    | 0.8       |
| 60°-70°   | 30.1    | 0.3       |
| 70°-80°   | 0.7     | 0.0       |
| 80°-90°   | 0.5     | 0.0       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-30°    | 10945.5 | 92.3      |
| 0°-40°    | 11501.9 | 97.0      |
| 0°-60°    | 11829.7 | 99.7      |
| 0°-90°    | 11861.0 | 100.0     |
| 90°-120°  | 0.0     | 0.0       |
| 90°-150°  | 0.0     | 0.0       |
| 90°-180°  | 0.0     | 0.0       |
| 0°-180°   | 11861.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 32635 |      |
| 5°  | 31747 | ###  |
| 15° | 21533 | 5701 |
| 25° | 4458  | 2325 |
| 35° | 824   | 556  |
| 45° | 283   | 232  |
| 55° | 103   | 96   |
| 65° | 30    | 30   |
| 75° | 0     | 1    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P774304

CATALOG NUMBER: LD6D95BD010-EU6DR3570959040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 32635.3 |
| 2.5°  | 32439.6 |
| 5°    | 31747.2 |
| 7.5°  | 30366.2 |
| 10°   | 28285.6 |
| 12.5° | 25356.2 |
| 15°   | 21533.2 |
| 17.5° | 16857.8 |
| 20°   | 11881.6 |
| 22.5° | 7576.4  |
| 25°   | 4458.3  |
| 27.5° | 2520.1  |
| 30°   | 1589.3  |
| 32.5° | 1115.9  |
| 35°   | 824.0   |
| 37.5° | 637.2   |
| 40°   | 503.7   |
| 42.5° | 388.0   |
| 45°   | 283.0   |
| 47.5° | 211.8   |
| 50°   | 163.7   |
| 52.5° | 129.9   |
| 55°   | 103.2   |
| 57.5° | 83.6    |
| 60°   | 65.9    |
| 62.5° | 48.1    |
| 65°   | 30.3    |
| 67.5° | 10.7    |
| 70°   | 1.8     |
| 72.5° | 1.8     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 1.8     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

## Scaled Data Report





— 0°-180°







(END OF REPORT)