

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774380

Luminaire Tested: LD6D95BD010-EU6DR4070959040-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4070959040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11002.8 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774380

CATALOG NUMBER: LD6D95BD010-EU6DR4070959040-6LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P774380

CATALOG NUMBER: LD6D95BD010-EU6DR4070959040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2798987
5°	2785385
10°	2632800
15°	2238208
20°	1525500
25°	636499
30°	200133
35°	93021
40°	51447
45°	23579
50°	11440
55°	6267
60°	3278
65°	1163
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23579 cd/sqm



TEST NUMBER: P774380

CATALOG NUMBER: LD6D95BD010-EU6DR4070959040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2371.3	21.6
10°-20°	5312.5	48.3
20°-30°	2659.2	24.2
30°-40°	487.5	4.4
40°-50°	134.5	1.2
50°-60°	31.6	0.3
60°-70°	6.1	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10343.0	94.0
0°-40°	10830.5	98.4
0°-60°	10996.6	99.9
0°-90°	11002.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11002.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25618	
5°	25396	###
15°	19787	5312
25°	5280	2659
35°	697	487
45°	153	134
55°	33	32
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774380

CATALOG NUMBER: LD6D95BD010-EU6DR4070959040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	25617.5
2.5°	25580.1
5°	25396.0
7.5°	24809.3
10°	23730.4
12.5°	22048.3
15°	19787.0
17.5°	16846.4
20°	13120.0
22.5°	8944.7
25°	5279.7
27.5°	2791.0
30°	1586.3
32.5°	1025.1
35°	697.4
37.5°	498.3
40°	360.7
42.5°	246.9
45°	152.6
47.5°	97.3
50°	67.3
52.5°	47.9
55°	32.9
57.5°	21.0
60°	15.0
62.5°	9.0
65°	4.5
67.5°	3.0
70°	1.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)