

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774735

Luminaire Tested: LD6D95BD010-EU6DR6570959027-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6570959027-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9293.9 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P774735
CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P774735

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	492847
5°	491605
10°	491186
15°	476040
20°	433380
25°	377660
30°	314111
35°	248887
40°	179631
45°	113486
50°	59150
55°	31443
60°	16517
65°	9079
70°	3808
75°	4197
80°	2926
85°	2479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 113486 cd/sqm



TEST NUMBER: P774735

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	798.0	8.6
10°-20°	2185.3	23.5
20°-30°	2671.2	28.7
30°-40°	2167.3	23.3
40°-50°	1080.0	11.6
50°-60°	301.2	3.2
60°-70°	68.5	0.7
70°-80°	17.8	0.2
80°-90°	4.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5654.5	60.8
0°-40°	7821.8	84.2
0°-60°	9203.1	99.0
0°-90°	9293.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9293.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8439	
5°	8385	798
15°	7873	2185
25°	5860	2671
35°	3491	2167
45°	1374	1080
55°	309	301
65°	66	68
75°	19	18
85°	4	5
90°	0	



TEST NUMBER: P774735

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8438.6
2.5°	8432.4
5°	8385.3
7.5°	8358.0
10°	8282.4
12.5°	8128.6
15°	7873.1
17.5°	7473.8
20°	6972.9
22.5°	6432.2
25°	5860.5
27.5°	5249.2
30°	4657.7
32.5°	4073.6
35°	3490.8
37.5°	2909.2
40°	2356.1
42.5°	1837.8
45°	1374.0
47.5°	957.3
50°	651.0
52.5°	448.9
55°	308.8
57.5°	208.3
60°	141.4
62.5°	98.0
65°	65.7
67.5°	33.5
70°	22.3
72.5°	21.1
75°	18.6
77.5°	12.4
80°	8.7
82.5°	6.2
85°	3.7
87.5°	2.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)