

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774387

Luminaire Tested: LD6D95BD010-EU6DR4070959040-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4070959040-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12345.8 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774387

CATALOG NUMBER: LD6D95BD010-EU6DR4070959040-6LBS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P774387

CATALOG NUMBER: LD6D95BD010-EU6DR4070959040-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3140624
5°	3125366
10°	2954144
15°	2511403
20°	1711699
25°	714197
30°	224558
35°	104372
40°	57722
45°	26469
50°	12850
55°	7029
60°	3671
65°	1293
70°	543
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26469 cd/sqm



TEST NUMBER: P774387

CATALOG NUMBER: LD6D95BD010-EU6DR4070959040-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2660.8	21.6
10°-20°	5960.9	48.3
20°-30°	2983.8	24.2
30°-40°	547.0	4.4
40°-50°	150.9	1.2
50°-60°	35.4	0.3
60°-70°	6.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11605.5	94.0
0°-40°	12152.4	98.4
0°-60°	12338.8	99.9
0°-90°	12345.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12345.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	28744	
5°	28496	###
15°	22202	5961
25°	5924	2984
35°	782	547
45°	171	151
55°	37	35
65°	5	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774387

CATALOG NUMBER: LD6D95BD010-EU6DR4070959040-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	28744.3
2.5°	28702.3
5°	28495.8
7.5°	27837.5
10°	26626.8
12.5°	24739.4
15°	22202.2
17.5°	18902.6
20°	14721.4
22.5°	10036.5
25°	5924.2
27.5°	3131.7
30°	1779.9
32.5°	1150.2
35°	782.5
37.5°	559.2
40°	404.7
42.5°	277.1
45°	171.3
47.5°	109.1
50°	75.6
52.5°	53.7
55°	36.9
57.5°	23.5
60°	16.8
62.5°	10.1
65°	5.0
67.5°	3.4
70°	1.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)