

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774279

Luminaire Tested: LD6D95BD010-EU6DR3570959030-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10014.2 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774279

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774279

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LB DP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96						
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88						
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84						
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81						
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78						
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75						
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72						
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70						
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3010571
5°	2939823
10°	2649564
15°	2056488
20°	1166403
25°	453784
30°	169299
35°	92794
40°	60646
45°	36914
50°	23491
55°	16611
60°	12150
65°	6593
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36914 cd/sqm



TEST NUMBER: P774279

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2465.2	24.6
10°-20°	4813.1	48.1
20°-30°	1963.0	19.6
30°-40°	469.8	4.7
40°-50°	195.8	2.0
50°-60°	81.0	0.8
60°-70°	25.4	0.3
70°-80°	0.6	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9241.3	92.3
0°-40°	9711.0	97.0
0°-60°	9987.8	99.7
0°-90°	10014.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10014.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27554	
5°	26804	###
15°	18180	4813
25°	3764	1963
35°	696	470
45°	239	196
55°	87	81
65°	26	25
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774279

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	27554.0
2.5°	27388.7
5°	26804.1
7.5°	25638.1
10°	23881.5
12.5°	21408.1
15°	18180.5
17.5°	14233.0
20°	10031.6
22.5°	6396.7
25°	3764.1
27.5°	2127.7
30°	1341.9
32.5°	942.2
35°	695.7
37.5°	537.9
40°	425.2
42.5°	327.6
45°	238.9
47.5°	178.8
50°	138.2
52.5°	109.7
55°	87.2
57.5°	70.6
60°	55.6
62.5°	40.6
65°	25.5
67.5°	9.0
70°	1.5
72.5°	1.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)