

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774589

Luminaire Tested: LD6D95BD010-EU6DR5570959030-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774589
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5570959030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11432.8 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774589

CATALOG NUMBER: LD6D95BD010-EU6DR5570959030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P774589

CATALOG NUMBER: LD6D95BD010-EU6DR5570959030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64		82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1400723
5°	1345092
10°	1340031
15°	1301536
20°	1167008
25°	964471
30°	728543
35°	528249
40°	338061
45°	154394
50°	50501
55°	21792
60°	9375
65°	1241
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 154394 cd/sqm



TEST NUMBER: P774589

CATALOG NUMBER: LD6D95BD010-EU6DR5570959030-6LBPD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1167.0	10.2
10°-20°	3184.9	27.9
20°-30°	3629.5	31.7
30°-40°	2470.8	21.6
40°-50°	851.4	7.4
50°-60°	117.7	1.0
60°-70°	11.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7981.4	69.8
0°-40°	10452.3	91.4
0°-60°	11421.4	99.9
0°-90°	11432.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11432.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12820	
5°	12264	###
15°	11506	3185
25°	8000	3630
35°	3960	2471
45°	999	851
55°	114	118
65°	5	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774589

CATALOG NUMBER: LD6D95BD010-EU6DR5570959030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	12820.0
2.5°	12526.1
5°	12264.0
7.5°	12135.3
10°	12078.2
12.5°	11887.5
15°	11506.3
17.5°	10901.0
20°	10036.8
22.5°	9039.2
25°	8000.2
27.5°	6918.4
30°	5774.6
32.5°	4805.5
35°	3960.4
37.5°	3156.6
40°	2370.2
42.5°	1642.6
45°	999.2
47.5°	538.5
50°	297.1
52.5°	176.3
55°	114.4
57.5°	73.1
60°	42.9
62.5°	19.1
65°	4.8
67.5°	1.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)