

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774322

Luminaire Tested: LD6D95BD010-EU6DR3570959050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774322
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11384.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774322

CATALOG NUMBER: LD6D95BD010-EU6DR3570959050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774322

CATALOG NUMBER: LD6D95BD010-EU6DR3570959050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3422386
5°	3341969
10°	3011992
15°	2337794
20°	1325964
25°	515859
30°	192450
35°	105492
40°	68947
45°	41967
50°	26721
55°	18878
60°	13811
65°	7497
70°	543
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41967 cd/sqm



TEST NUMBER: P774322

CATALOG NUMBER: LD6D95BD010-EU6DR3570959050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2802.4	24.6
10°-20°	5471.5	48.1
20°-30°	2231.5	19.6
30°-40°	534.0	4.7
40°-50°	222.6	2.0
50°-60°	92.1	0.8
60°-70°	28.8	0.3
70°-80°	0.7	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10505.4	92.3
0°-40°	11039.4	97.0
0°-60°	11354.1	99.7
0°-90°	11384.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11384.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	31323	
5°	30471	###
15°	20667	5472
25°	4279	2231
35°	791	534
45°	272	223
55°	99	92
65°	29	29
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774322

CATALOG NUMBER: LD6D95BD010-EU6DR3570959050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	31323.1
2.5°	31135.2
5°	30470.7
7.5°	29145.1
10°	27148.2
12.5°	24336.6
15°	20667.4
17.5°	16180.0
20°	11403.9
22.5°	7271.8
25°	4279.0
27.5°	2418.8
30°	1525.4
32.5°	1071.0
35°	790.9
37.5°	611.5
40°	483.4
42.5°	372.4
45°	271.6
47.5°	203.3
50°	157.2
52.5°	124.7
55°	99.1
57.5°	80.3
60°	63.2
62.5°	46.1
65°	29.0
67.5°	10.2
70°	1.7
72.5°	1.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)