

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774395

Luminaire Tested: LD6D95BD010-EU6DR4070959050-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4070959050-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13056.0 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774395

CATALOG NUMBER: LD6D95BD010-EU6DR4070959050-6LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P774395

CATALOG NUMBER: LD6D95BD010-EU6DR4070959050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3321276
5°	3305139
10°	3124081
15°	2655862
20°	1810159
25°	755271
30°	237477
35°	110374
40°	61046
45°	27983
50°	13581
55°	7448
60°	3890
65°	1370
70°	575
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27983 cd/sqm



TEST NUMBER: P774395

CATALOG NUMBER: LD6D95BD010-EU6DR4070959050-6LBPD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2813.8	21.6
10°-20°	6303.8	48.3
20°-30°	3155.4	24.2
30°-40°	578.4	4.4
40°-50°	159.6	1.2
50°-60°	37.5	0.3
60°-70°	7.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12273.0	94.0
0°-40°	12851.5	98.4
0°-60°	13048.5	99.9
0°-90°	13056.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13056.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	30398	
5°	30135	###
15°	23479	6304
25°	6265	3155
35°	828	578
45°	181	160
55°	39	38
65°	5	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774395

CATALOG NUMBER: LD6D95BD010-EU6DR4070959050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	30397.7
2.5°	30353.3
5°	30134.9
7.5°	29438.8
10°	28158.5
12.5°	26162.5
15°	23479.3
17.5°	19989.9
20°	15568.2
22.5°	10613.8
25°	6264.9
27.5°	3311.8
30°	1882.3
32.5°	1216.4
35°	827.5
37.5°	591.3
40°	428.0
42.5°	293.0
45°	181.1
47.5°	115.4
50°	79.9
52.5°	56.8
55°	39.1
57.5°	24.9
60°	17.8
62.5°	10.7
65°	5.3
67.5°	3.6
70°	1.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)