

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774556

Luminaire Tested: LD6D95BD010-EU6DR5070959050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5070959050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12355.4 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774556

CATALOG NUMBER: LD6D95BD010-EU6DR5070959050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774556

CATALOG NUMBER: LD6D95BD010-EU6DR5070959050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2175130
5°	2152323
10°	2116877
15°	1927582
20°	1603973
25°	1138578
30°	602658
35°	245584
40°	91212
45°	41751
50°	17117
55°	8953
60°	4392
65°	1293
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41751 cd/sqm



TEST NUMBER: P774556

CATALOG NUMBER: LD6D95BD010-EU6DR5070959050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1854.9	15.0
10°-20°	4687.6	37.9
20°-30°	4210.7	34.1
30°-40°	1318.4	10.7
40°-50°	230.8	1.9
50°-60°	46.0	0.4
60°-70°	6.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10753.2	87.0
0°-40°	12071.6	97.7
0°-60°	12348.4	99.9
0°-90°	12355.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12355.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19908	
5°	19624	###
15°	17041	4688
25°	9444	4211
35°	1841	1318
45°	270	231
55°	47	46
65°	5	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774556

CATALOG NUMBER: LD6D95BD010-EU6DR5070959050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	19907.7
2.5°	19808.7
5°	19624.0
7.5°	19342.1
10°	19080.2
12.5°	18241.0
15°	17040.9
17.5°	15516.9
20°	13794.9
22.5°	11802.6
25°	9444.4
27.5°	6943.6
30°	4776.8
32.5°	3110.1
35°	1841.2
37.5°	1057.4
40°	639.5
42.5°	416.2
45°	270.2
47.5°	164.5
50°	100.7
52.5°	68.8
55°	47.0
57.5°	31.9
60°	20.1
62.5°	11.7
65°	5.0
67.5°	1.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)