

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774633

Luminaire Tested: LD6D95BD010-EU6DR5570959050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5570959050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13461.7 lumens
Efficiency: N/A
Efficacy: 135.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774633

CATALOG NUMBER: LD6D95BD010-EU6DR5570959050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P774633

CATALOG NUMBER: LD6D95BD010-EU6DR5570959050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65		
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57		
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54		
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1649324
5°	1583818
10°	1577845
15°	1532517
20°	1374124
25°	1135637
30°	857836
35°	622004
40°	398051
45°	181806
50°	59459
55°	25659
60°	11035
65°	1448
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 181806 cd/sqm



TEST NUMBER: P774633

CATALOG NUMBER: LD6D95BD010-EU6DR5570959050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1374.1	10.2
10°-20°	3750.2	27.9
20°-30°	4273.7	31.7
30°-40°	2909.3	21.6
40°-50°	1002.5	7.4
50°-60°	138.6	1.0
60°-70°	13.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9397.9	69.8
0°-40°	12307.3	91.4
0°-60°	13448.4	99.9
0°-90°	13461.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13461.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15095	
5°	14441	###
15°	13548	3750
25°	9420	4274
35°	4663	2909
45°	1177	1003
55°	135	139
65°	6	13
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774633

CATALOG NUMBER: LD6D95BD010-EU6DR5570959050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	15095.3
2.5°	14749.2
5°	14440.6
7.5°	14289.0
10°	14221.7
12.5°	13997.2
15°	13548.3
17.5°	12835.6
20°	11818.1
22.5°	10643.4
25°	9420.0
27.5°	8146.2
30°	6799.4
32.5°	5658.4
35°	4663.3
37.5°	3716.8
40°	2790.8
42.5°	1934.1
45°	1176.6
47.5°	634.1
50°	349.8
52.5°	207.6
55°	134.7
57.5°	86.0
60°	50.5
62.5°	22.4
65°	5.6
67.5°	1.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)