

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761105

Luminaire Tested: LD6D15D010-EU6DR250215IC9027-6LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761105  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR250215IC9027-6LBCSSQMMS  
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1111.6 lumens  
Efficiency: N/A  
Efficacy: 70.4 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761105

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9027-6LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P761105

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9027-6LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 |  | 103 | 102 | 101 |  | 99  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98  |  | 99  | 97  | 96  |  | 97  |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 93  |  | 96  | 93  | 91  |  | 94  |
| 4   | 103 | 97  | 93  | 90  | 102 | 96  | 93  | 90  | 94  | 91  | 89  |  | 93  | 90  | 88  |  | 91  |
| 5   | 100 | 93  | 89  | 86  | 98  | 93  | 89  | 86  | 91  | 87  | 85  |  | 89  | 86  | 84  |  | 88  |
| 6   | 97  | 90  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 81  |  | 87  | 83  | 81  |  | 85  |
| 7   | 93  | 87  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 78  |  | 84  | 80  | 78  |  | 83  |
| 8   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 76  |  | 81  | 78  | 75  |  | 80  |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 80  | 76  | 73  |  | 79  | 75  | 73  |  | 78  |
| 10  | 85  | 78  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  |  | 76  | 73  | 71  |  | 76  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 460643 |
| 5°  | 429039 |
| 10° | 306045 |
| 15° | 180249 |
| 20° | 112157 |
| 25° | 61556  |
| 30° | 28147  |
| 35° | 10657  |
| 40° | 4835   |
| 45° | 2905   |
| 50° | 1207   |
| 55° | 781    |
| 60° | 546    |
| 65° | 362    |
| 70° | 64     |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2905 cd/sqm



TEST NUMBER: P761105

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9027-6LBCSSQMMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 336.2  | 30.2      |
| 10°-20°   | 455.3  | 41.0      |
| 20°-30°   | 241.0  | 21.7      |
| 30°-40°   | 59.5   | 5.4       |
| 40°-50°   | 14.5   | 1.3       |
| 50°-60°   | 3.8    | 0.3       |
| 60°-70°   | 1.3    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1032.5 | 92.9      |
| 0°-40°    | 1092.0 | 98.2      |
| 0°-60°    | 1110.3 | 99.9      |
| 0°-90°    | 1111.6 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1111.6 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4216 |      |
| 5°  | 3912 | 336  |
| 15° | 1594 | 455  |
| 25° | 511  | 241  |
| 35° | 80   | 59   |
| 45° | 19   | 15   |
| 55° | 4    | 4    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P761105

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9027-6LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 4216.0 |
| 2.5°  | 4146.7 |
| 5°    | 3911.8 |
| 7.5°  | 3439.7 |
| 10°   | 2758.5 |
| 12.5° | 2085.3 |
| 15°   | 1593.5 |
| 17.5° | 1241.9 |
| 20°   | 964.6  |
| 22.5° | 723.4  |
| 25°   | 510.6  |
| 27.5° | 342.4  |
| 30°   | 223.1  |
| 32.5° | 135.7  |
| 35°   | 79.9   |
| 37.5° | 48.9   |
| 40°   | 33.9   |
| 42.5° | 25.9   |
| 45°   | 18.8   |
| 47.5° | 11.3   |
| 50°   | 7.1    |
| 52.5° | 5.2    |
| 55°   | 4.1    |
| 57.5° | 3.2    |
| 60°   | 2.5    |
| 62.5° | 1.9    |
| 65°   | 1.4    |
| 67.5° | 0.5    |
| 70°   | 0.2    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)