

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761746

Luminaire Tested: LD6D15D010-EU6DR650215IC9040-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761746
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9040-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1333.3 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761746

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P761746

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70698
5°	70522
10°	70460
15°	68288
20°	62171
25°	54176
30°	45063
35°	35706
40°	25769
45°	16280
50°	8486
55°	4511
60°	2371
65°	1313
70°	546
75°	609
80°	437
85°	335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16280 cd/sqm



TEST NUMBER: P761746

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.5	8.6
10°-20°	313.5	23.5
20°-30°	383.2	28.7
30°-40°	310.9	23.3
40°-50°	154.9	11.6
50°-60°	43.2	3.2
60°-70°	9.8	0.7
70°-80°	2.6	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.2	60.8
0°-40°	1122.1	84.2
0°-60°	1320.2	99.0
0°-90°	1333.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1333.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1210	
5°	1203	114
15°	1129	313
25°	841	383
35°	501	311
45°	197	155
55°	44	43
65°	10	10
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P761746

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1210.5
2.5°	1209.7
5°	1202.9
7.5°	1199.0
10°	1188.1
12.5°	1166.1
15°	1129.4
17.5°	1072.2
20°	1000.3
22.5°	922.7
25°	840.7
27.5°	753.0
30°	668.2
32.5°	584.4
35°	500.8
37.5°	417.3
40°	338.0
42.5°	263.6
45°	197.1
47.5°	137.3
50°	93.4
52.5°	64.4
55°	44.3
57.5°	29.9
60°	20.3
62.5°	14.0
65°	9.5
67.5°	4.8
70°	3.2
72.5°	3.0
75°	2.7
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.5
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)