

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768346

Luminaire Tested: LD6D55D010-EU6DR5555659030-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR5555659030-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6543.8 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768346

CATALOG NUMBER: LD6D55D010-EU6DR5555659030-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P768346

CATALOG NUMBER: LD6D55D010-EU6DR5555659030-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	801744
5°	769907
10°	767005
15°	744964
20°	667976
25°	552038
30°	416995
35°	302352
40°	193506
45°	88369
50°	28897
55°	12477
60°	5376
65°	698
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 88369 cd/sqm



TEST NUMBER: P768346

CATALOG NUMBER: LD6D55D010-EU6DR5555659030-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	668.0	10.2
10°-20°	1823.0	27.9
20°-30°	2077.4	31.7
30°-40°	1414.2	21.6
40°-50°	487.3	7.4
50°-60°	67.4	1.0
60°-70°	6.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4568.4	69.8
0°-40°	5982.6	91.4
0°-60°	6537.3	99.9
0°-90°	6543.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6543.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7338	
5°	7020	668
15°	6586	1823
25°	4579	2077
35°	2267	1414
45°	572	487
55°	66	67
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768346

CATALOG NUMBER: LD6D55D010-EU6DR5555659030-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	7337.9
2.5°	7169.7
5°	7019.7
7.5°	6946.0
10°	6913.3
12.5°	6804.2
15°	6585.9
17.5°	6239.5
20°	5744.9
22.5°	5173.8
25°	4579.1
27.5°	3959.9
30°	3305.2
32.5°	2750.6
35°	2266.8
37.5°	1806.7
40°	1356.7
42.5°	940.2
45°	571.9
47.5°	308.2
50°	170.0
52.5°	100.9
55°	65.5
57.5°	41.8
60°	24.6
62.5°	10.9
65°	2.7
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)