

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769188

Luminaire Tested: LD6D60D010-EU6DR6055659024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P769188
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR6055659024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4909.6 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769188

CATALOG NUMBER: LD6D60D010-EU6DR6055659024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P769188

CATALOG NUMBER: LD6D60D010-EU6DR6055659024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	637078
5°	652738
10°	660630
15°	629338
20°	554877
25°	448806
30°	303574
35°	152123
40°	24675
45°	24151
50°	24630
55°	25011
60°	25698
65°	26293
70°	26898
75°	27229
80°	26238
85°	21938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 27229 cd/sqm



TEST NUMBER: P769188

CATALOG NUMBER: LD6D60D010-EU6DR6055659024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	568.8	11.6
10°-20°	1538.9	31.3
20°-30°	1655.8	33.7
30°-40°	719.7	14.7
40°-50°	120.9	2.5
50°-60°	117.5	2.4
60°-70°	100.5	2.0
70°-80°	67.3	1.4
80°-90°	20.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3763.5	76.7
0°-40°	4483.3	91.3
0°-60°	4721.7	96.2
0°-90°	4909.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4909.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5831	
5°	5951	569
15°	5564	1539
25°	3723	1656
35°	1140	720
45°	156	121
55°	131	118
65°	102	101
75°	64	67
85°	18	20
90°	0	



TEST NUMBER: P769188

CATALOG NUMBER: LD6D60D010-EU6DR6055659024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5830.8
2.5°	5994.7
5°	5951.4
7.5°	5965.1
10°	5954.5
12.5°	5831.6
15°	5563.7
17.5°	5204.0
20°	4772.2
22.5°	4310.1
25°	3722.8
27.5°	2977.6
30°	2406.2
32.5°	1854.6
35°	1140.5
37.5°	487.9
40°	173.0
42.5°	159.4
45°	156.3
47.5°	151.0
50°	144.9
52.5°	138.1
55°	131.3
57.5°	124.4
60°	117.6
62.5°	110.0
65°	101.7
67.5°	93.3
70°	84.2
72.5°	74.4
75°	64.5
77.5°	53.1
80°	41.7
82.5°	29.6
85°	17.5
87.5°	6.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)