

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768824

Luminaire Tested: LD6D60D010-EU6DR3555659030-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR3555659030-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5860.2 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768824

CATALOG NUMBER: LD6D60D010-EU6DR3555659030-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P768824

CATALOG NUMBER: LD6D60D010-EU6DR3555659030-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1761764
5°	1720367
10°	1550508
15°	1203442
20°	682580
25°	265548
30°	99064
35°	54300
40°	35501
45°	21602
50°	13751
55°	9715
60°	7102
65°	3852
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21602 cd/sqm



TEST NUMBER: P768824

CATALOG NUMBER: LD6D60D010-EU6DR3555659030-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1442.6	24.6
10°-20°	2816.6	48.1
20°-30°	1148.7	19.6
30°-40°	274.9	4.7
40°-50°	114.6	2.0
50°-60°	47.4	0.8
60°-70°	14.8	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5407.9	92.3
0°-40°	5682.8	97.0
0°-60°	5844.8	99.7
0°-90°	5860.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5860.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16124	
5°	15686	###
15°	10639	2817
25°	2203	1149
35°	407	275
45°	140	115
55°	51	47
65°	15	15
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768824

CATALOG NUMBER: LD6D60D010-EU6DR3555659030-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	16124.4
2.5°	16027.7
5°	15685.6
7.5°	15003.2
10°	13975.3
12.5°	12527.9
15°	10639.1
17.5°	8329.1
20°	5870.5
22.5°	3743.3
25°	2202.7
27.5°	1245.1
30°	785.2
32.5°	551.3
35°	407.1
37.5°	314.8
40°	248.9
42.5°	191.7
45°	139.8
47.5°	104.6
50°	80.9
52.5°	64.2
55°	51.0
57.5°	41.3
60°	32.5
62.5°	23.7
65°	14.9
67.5°	5.3
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)