

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774153

Luminaire Tested: LD6D95BD010-EU6DR2570959040-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR2570959040-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10567.9 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774153

CATALOG NUMBER: LD6D95BD010-EU6DR2570959040-6LBS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P774153

CATALOG NUMBER: LD6D95BD010-EU6DR2570959040-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4379357
5°	4078819
10°	2909533
15°	1713603
20°	1066222
25°	585142
30°	267605
35°	101344
40°	45898
45°	27597
50°	11457
55°	7372
60°	5157
65°	3490
70°	543
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27597 cd/sqm



TEST NUMBER: P774153

CATALOG NUMBER: LD6D95BD010-EU6DR2570959040-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3196.1	30.2
10°-20°	4328.9	41.0
20°-30°	2290.8	21.7
30°-40°	565.5	5.4
40°-50°	138.0	1.3
50°-60°	36.3	0.3
60°-70°	12.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9815.7	92.9
0°-40°	10381.2	98.2
0°-60°	10555.5	99.9
0°-90°	10567.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10567.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	40082	
5°	37189	###
15°	15149	4329
25°	4854	2291
35°	760	565
45°	179	138
55°	39	36
65°	14	12
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774153

CATALOG NUMBER: LD6D95BD010-EU6DR2570959040-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	40081.7
2.5°	39422.9
5°	37189.0
7.5°	32700.8
10°	26224.7
12.5°	19824.3
15°	15149.2
17.5°	11806.7
20°	9170.0
22.5°	6877.1
25°	4853.7
27.5°	3254.9
30°	2121.1
32.5°	1290.5
35°	759.8
37.5°	465.0
40°	321.8
42.5°	246.0
45°	178.6
47.5°	107.8
50°	67.4
52.5°	48.9
55°	38.7
57.5°	30.3
60°	23.6
62.5°	18.5
65°	13.5
67.5°	5.1
70°	1.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)