

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768694

Luminaire Tested: LD6D60D010-EU6DR2555659040-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR2555659040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5114.5 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768694

CATALOG NUMBER: LD6D60D010-EU6DR2555659040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P768694

CATALOG NUMBER: LD6D60D010-EU6DR2555659040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2119451
5°	1974009
10°	1408108
15°	829326
20°	516019
25°	283186
30°	129507
35°	49045
40°	22207
45°	13350
50°	5541
55°	3581
60°	2491
65°	1680
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13350 cd/sqm



TEST NUMBER: P768694

CATALOG NUMBER: LD6D60D010-EU6DR2555659040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1546.8	30.2
10°-20°	2095.0	41.0
20°-30°	1108.7	21.7
30°-40°	273.7	5.4
40°-50°	66.8	1.3
50°-60°	17.6	0.3
60°-70°	5.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4750.5	92.9
0°-40°	5024.1	98.2
0°-60°	5108.5	99.9
0°-90°	5114.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5114.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19398	
5°	17998	###
15°	7332	2095
25°	2349	1109
35°	368	274
45°	86	67
55°	19	18
65°	6	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768694

CATALOG NUMBER: LD6D60D010-EU6DR2555659040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	19398.1
2.5°	19079.3
5°	17998.2
7.5°	15826.0
10°	12691.8
12.5°	9594.3
15°	7331.7
17.5°	5714.0
20°	4438.0
22.5°	3328.3
25°	2349.0
27.5°	1575.3
30°	1026.5
32.5°	624.6
35°	367.7
37.5°	225.0
40°	155.7
42.5°	119.0
45°	86.4
47.5°	52.2
50°	32.6
52.5°	23.6
55°	18.8
57.5°	14.7
60°	11.4
62.5°	9.0
65°	6.5
67.5°	2.4
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)