

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769812

Luminaire Tested: LD6D65D010-EU6DR5055659024-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR5055659024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6141.5 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769812

CATALOG NUMBER: LD6D65D010-EU6DR5055659024-6LBSQW1B

Luminous Intensity Polar Plot



TEST NUMBER: P769812

CATALOG NUMBER: LD6D65D010-EU6DR5055659024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1081179
5°	1069844
10°	1052226
15°	958141
20°	797283
25°	565950
30°	299563
35°	122072
40°	45342
45°	20752
50°	8516
55°	4457
60°	2185
65°	646
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20752 cd/sqm



TEST NUMBER: P769812

CATALOG NUMBER: LD6D65D010-EU6DR5055659024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	922.0	15.0
10°-20°	2330.1	37.9
20°-30°	2093.0	34.1
30°-40°	655.3	10.7
40°-50°	114.8	1.9
50°-60°	22.9	0.4
60°-70°	3.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5345.1	87.0
0°-40°	6000.4	97.7
0°-60°	6138.0	99.9
0°-90°	6141.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6141.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9895	
5°	9754	922
15°	8470	2330
25°	4694	2093
35°	915	655
45°	134	115
55°	23	23
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769812

CATALOG NUMBER: LD6D65D010-EU6DR5055659024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	9895.4
2.5°	9846.2
5°	9754.4
7.5°	9614.3
10°	9484.1
12.5°	9067.0
15°	8470.5
17.5°	7712.9
20°	6857.0
22.5°	5866.7
25°	4694.5
27.5°	3451.4
30°	2374.4
32.5°	1545.9
35°	915.2
37.5°	525.6
40°	317.9
42.5°	206.9
45°	134.3
47.5°	81.8
50°	50.1
52.5°	34.2
55°	23.4
57.5°	15.9
60°	10.0
62.5°	5.8
65°	2.5
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)