

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774614

Luminaire Tested: LD6D95BD010-EU6DR5570959040-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5570959040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9535.4 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774614

CATALOG NUMBER: LD6D95BD010-EU6DR5570959040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P774614

CATALOG NUMBER: LD6D95BD010-EU6DR5570959040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64		82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1168260
5°	1121854
10°	1117628
15°	1085520
20°	973332
25°	804409
30°	607628
35°	440577
40°	281951
45°	128775
50°	42121
55°	18173
60°	7823
65°	1034
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 128775 cd/sqm



TEST NUMBER: P774614

CATALOG NUMBER: LD6D95BD010-EU6DR5570959040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	973.3	10.2
10°-20°	2656.3	27.9
20°-30°	3027.2	31.7
30°-40°	2060.8	21.6
40°-50°	710.1	7.4
50°-60°	98.2	1.0
60°-70°	9.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6656.8	69.8
0°-40°	8717.6	91.4
0°-60°	9525.9	99.9
0°-90°	9535.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9535.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10692	
5°	10229	973
15°	9597	2656
25°	6672	3027
35°	3303	2061
45°	833	710
55°	95	98
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774614

CATALOG NUMBER: LD6D95BD010-EU6DR5570959040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	10692.4
2.5°	10447.3
5°	10228.6
7.5°	10121.3
10°	10073.6
12.5°	9914.6
15°	9596.6
17.5°	9091.8
20°	8371.1
22.5°	7539.0
25°	6672.5
27.5°	5770.2
30°	4816.2
32.5°	4008.0
35°	3303.1
37.5°	2632.7
40°	1976.8
42.5°	1370.0
45°	833.4
47.5°	449.2
50°	247.8
52.5°	147.1
55°	95.4
57.5°	60.9
60°	35.8
62.5°	15.9
65°	4.0
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)