

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772468

Luminaire Tested: LD6D80BD010-EU6DR7070959027-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR7070959027-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9406.6 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772468

CATALOG NUMBER: LD6D80BD010-EU6DR7070959027-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P772468

CATALOG NUMBER: LD6D80BD010-EU6DR7070959027-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	811206
5°	809183
10°	807434
15°	807200
20°	799318
25°	750858
30°	669385
35°	533704
40°	354378
45°	211875
50°	109841
55°	57738
60°	20432
65°	336
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 211875 cd/sqm



TEST NUMBER: P772468

CATALOG NUMBER: LD6D80BD010-EU6DR7070959027-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	701.6	7.5
10°-20°	2012.3	21.4
20°-30°	2838.7	30.2
30°-40°	2450.6	26.1
40°-50°	1097.4	11.7
50°-60°	287.3	3.1
60°-70°	18.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5552.6	59.0
0°-40°	8003.2	85.1
0°-60°	9387.9	99.8
0°-90°	9406.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9406.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7424	
5°	7378	702
15°	7136	2012
25°	6228	2839
35°	4001	2451
45°	1371	1097
55°	303	287
65°	1	19
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P772468

CATALOG NUMBER: LD6D80BD010-EU6DR7070959027-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7424.5
2.5°	7416.5
5°	7377.8
7.5°	7345.8
10°	7277.7
12.5°	7216.3
15°	7136.1
17.5°	7044.0
20°	6874.5
22.5°	6595.4
25°	6228.3
27.5°	5802.4
30°	5305.7
32.5°	4698.2
35°	4001.3
37.5°	3232.3
40°	2484.6
42.5°	1887.8
45°	1371.2
47.5°	945.3
50°	646.2
52.5°	445.9
55°	303.1
57.5°	182.9
60°	93.5
62.5°	29.4
65°	1.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)