

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772050

Luminaire Tested: LD6D80BD010-EU6DR4070959050-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR4070959050-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10134.7 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772050

CATALOG NUMBER: LD6D80BD010-EU6DR4070959050-6LBCSSQMB

Luminous Intensity Polar Plot



TEST NUMBER: P772050

CATALOG NUMBER: LD6D80BD010-EU6DR4070959050-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2578139
5°	2565612
10°	2425064
15°	2061612
20°	1405134
25°	586287
30°	184350
35°	85685
40°	47382
45°	21725
50°	10539
55°	5772
60°	3016
65°	1060
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21725 cd/sqm



TEST NUMBER: P772050

CATALOG NUMBER: LD6D80BD010-EU6DR4070959050-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2184.2	21.6
10°-20°	4893.3	48.3
20°-30°	2449.4	24.2
30°-40°	449.0	4.4
40°-50°	123.9	1.2
50°-60°	29.1	0.3
60°-70°	5.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9527.0	94.0
0°-40°	9976.0	98.4
0°-60°	10128.9	99.9
0°-90°	10134.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10134.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23596	
5°	23392	###
15°	18226	4893
25°	4863	2449
35°	642	449
45°	141	124
55°	30	29
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P772050

CATALOG NUMBER: LD6D80BD010-EU6DR4070959050-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	23596.2
2.5°	23561.8
5°	23392.2
7.5°	22851.9
10°	21858.0
12.5°	20308.6
15°	18225.8
17.5°	15517.2
20°	12084.8
22.5°	8239.0
25°	4863.2
27.5°	2570.8
30°	1461.2
32.5°	944.2
35°	642.4
37.5°	459.0
40°	332.2
42.5°	227.4
45°	140.6
47.5°	89.6
50°	62.0
52.5°	44.1
55°	30.3
57.5°	19.3
60°	13.8
62.5°	8.3
65°	4.1
67.5°	2.8
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)