

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774770

Luminaire Tested: LD6D95BD010-EU6DR6570959040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774770
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6570959040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7719.2 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774770

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P774770

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	830393
5°	831086
10°	860344
15°	861767
20°	793400
25°	676017
30°	517510
35°	365615
40°	215813
45°	87612
50°	31752
55°	17697
60°	10139
65°	5584
70°	5878
75°	4559
80°	4782
85°	4012

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 87612 cd/sqm



TEST NUMBER: P774770

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	731.8	9.5
10°-20°	2111.0	27.3
20°-30°	2532.8	32.8
30°-40°	1702.1	22.1
40°-50°	509.5	6.6
50°-60°	89.9	1.2
60°-70°	25.5	0.3
70°-80°	12.5	0.2
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5375.6	69.6
0°-40°	7077.7	91.7
0°-60°	7677.2	99.5
0°-90°	7719.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7719.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7600	
5°	7578	732
15°	7618	2111
25°	5608	2533
35°	2741	1702
45°	567	510
55°	93	90
65°	22	26
75°	11	13
85°	3	4
90°	0	



TEST NUMBER: P774770

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7600.1
2.5°	7632.5
5°	7577.5
7.5°	7691.9
10°	7754.6
12.5°	7739.5
15°	7618.5
17.5°	7322.6
20°	6823.6
22.5°	6236.1
25°	5607.5
27.5°	4897.9
30°	4101.9
32.5°	3380.5
35°	2741.1
37.5°	2109.3
40°	1513.1
42.5°	988.2
45°	567.0
47.5°	300.2
50°	186.8
52.5°	129.6
55°	92.9
57.5°	67.0
60°	46.4
62.5°	30.2
65°	21.6
67.5°	19.4
70°	18.4
72.5°	14.0
75°	10.8
77.5°	9.7
80°	7.6
82.5°	5.4
85°	3.2
87.5°	2.2
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)