

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772571

Luminaire Tested: LD6D85BD010-EU6DR2570959035-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR2570959035-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8545.5 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772571

CATALOG NUMBER: LD6D85BD010-EU6DR2570959035-6LBCSSQMMS

Luminous Intensity Polar Plot



TEST NUMBER: P772571

CATALOG NUMBER: LD6D85BD010-EU6DR2570959035-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3541261
5°	3298240
10°	2352716
15°	1385659
20°	862175
25°	473170
30°	216396
35°	81950
40°	37112
45°	22312
50°	9264
55°	5962
60°	4174
65°	2818
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22312 cd/sqm



TEST NUMBER: P772571

CATALOG NUMBER: LD6D85BD010-EU6DR2570959035-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2584.4	30.2
10°-20°	3500.4	41.0
20°-30°	1852.4	21.7
30°-40°	457.3	5.4
40°-50°	111.6	1.3
50°-60°	29.3	0.3
60°-70°	9.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7937.3	92.9
0°-40°	8394.5	98.2
0°-60°	8535.4	99.9
0°-90°	8545.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8545.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	32411	
5°	30072	###
15°	12250	3500
25°	3925	1852
35°	614	457
45°	144	112
55°	31	29
65°	11	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P772571

CATALOG NUMBER: LD6D85BD010-EU6DR2570959035-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	32411.1
2.5°	31878.4
5°	30072.0
7.5°	26442.7
10°	21205.9
12.5°	16030.5
15°	12250.0
17.5°	9547.2
20°	7415.1
22.5°	5561.0
25°	3924.9
27.5°	2632.0
30°	1715.2
32.5°	1043.5
35°	614.4
37.5°	376.0
40°	260.2
42.5°	198.9
45°	144.4
47.5°	87.2
50°	54.5
52.5°	39.5
55°	31.3
57.5°	24.5
60°	19.1
62.5°	15.0
65°	10.9
67.5°	4.1
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)