

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773284

Luminaire Tested: LD6D85BD010-EU6DR7070959035-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773284
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR7070959035-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8634.5 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773284

CATALOG NUMBER: LD6D85BD010-EU6DR7070959035-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P773284

CATALOG NUMBER: LD6D85BD010-EU6DR7070959035-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	74	69	87	79	73	69	77	72	68		75	71	67		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	77	66	60	56	75	66	60	56	65	59	55		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1060671
5°	1029154
10°	1000469
15°	987336
20°	921974
25°	692630
30°	489628
35°	173438
40°	91197
45°	97130
50°	100577
55°	102465
60°	103120
65°	100931
70°	95262
75°	88230
80°	78336
85°	63559

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 57.5°

Luminance: 103140 cd/sqm



TEST NUMBER: P773284

CATALOG NUMBER: LD6D85BD010-EU6DR7070959035-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	885.1	10.3
10°-20°	2427.7	28.1
20°-30°	2673.7	31.0
30°-40°	1021.6	11.8
40°-50°	482.3	5.6
50°-60°	479.5	5.6
60°-70°	383.9	4.4
70°-80°	220.7	2.6
80°-90°	60.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5986.5	69.3
0°-40°	7008.0	81.2
0°-60°	7969.9	92.3
0°-90°	8634.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8634.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9708	
5°	9383	885
15°	8729	2428
25°	5745	2674
35°	1300	1022
45°	629	482
55°	538	480
65°	390	384
75°	209	221
85°	51	60
90°	0	



TEST NUMBER: P773284

CATALOG NUMBER: LD6D85BD010-EU6DR7070959035-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	9707.7
2.5°	9606.2
5°	9383.4
7.5°	9197.4
10°	9017.6
12.5°	8865.4
15°	8728.6
17.5°	8398.2
20°	7929.4
22.5°	6918.0
25°	5745.3
27.5°	5001.4
30°	3880.9
32.5°	2506.8
35°	1300.3
37.5°	702.4
40°	639.4
42.5°	634.8
45°	628.6
47.5°	614.8
50°	591.7
52.5°	565.6
55°	537.9
57.5°	507.2
60°	471.9
62.5°	431.9
65°	390.4
67.5°	344.3
70°	298.2
72.5°	252.1
75°	209.0
77.5°	164.5
80°	124.5
82.5°	87.6
85°	50.7
87.5°	20.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)