

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774772

Luminaire Tested: LD6D95BD010-EU6DR6570959040-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P774772  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D95BD010-EU6DR6570959040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10881.1 lumens  
Efficiency: N/A  
Efficacy: 109.7 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P774772

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P774772

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 82  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 83  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 72  |  | 77  |
| 6   | 87  | 78  | 72  | 68  | 86  | 77  | 72  | 68  | 76  | 71  | 67  |  | 74  | 70  | 67  |  | 73  |
| 7   | 83  | 73  | 67  | 63  | 81  | 73  | 67  | 63  | 71  | 66  | 62  |  | 70  | 66  | 62  |  | 69  |
| 8   | 79  | 69  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 58  |  | 66  | 62  | 58  |  | 65  |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 58  | 55  |  | 63  | 58  | 55  |  | 62  |
| 10  | 71  | 61  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 51  |  | 59  | 55  | 51  |  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1170532 |
| 5°  | 1171494 |
| 10° | 1212743 |
| 15° | 1214743 |
| 20° | 1118382 |
| 25° | 952910  |
| 30° | 729490  |
| 35° | 515378  |
| 40° | 304215  |
| 45° | 123506  |
| 50° | 44773   |
| 55° | 24935   |
| 60° | 14313   |
| 65° | 7859    |
| 70° | 8274    |
| 75° | 6417    |
| 80° | 6733    |
| 85° | 5767    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 123506 cd/sqm



TEST NUMBER: P774772

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBDP1LI

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 1031.6  | 9.5       |
| 10°-20°   | 2975.7  | 27.3      |
| 20°-30°   | 3570.2  | 32.8      |
| 30°-40°   | 2399.3  | 22.1      |
| 40°-50°   | 718.2   | 6.6       |
| 50°-60°   | 126.8   | 1.2       |
| 60°-70°   | 36.0    | 0.3       |
| 70°-80°   | 17.7    | 0.2       |
| 80°-90°   | 5.6     | 0.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-30°    | 7577.5  | 69.6      |
| 0°-40°    | 9976.8  | 91.7      |
| 0°-60°    | 10821.8 | 99.5      |
| 0°-90°    | 10881.1 | 100.0     |
| 90°-120°  | 0.0     | 0.0       |
| 90°-150°  | 0.0     | 0.0       |
| 90°-180°  | 0.0     | 0.0       |
| 0°-180°   | 10881.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 10713 |      |
| 5°  | 10681 | ###  |
| 15° | 10739 | 2976 |
| 25° | 7904  | 3570 |
| 35° | 3864  | 2399 |
| 45° | 799   | 718  |
| 55° | 131   | 127  |
| 65° | 30    | 36   |
| 75° | 15    | 18   |
| 85° | 5     | 6    |
| 90° | 0     |      |



TEST NUMBER: P774772

CATALOG NUMBER: LD6D95BD010-EU6DR6570959040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 10713.2 |
| 2.5°  | 10758.8 |
| 5°    | 10681.2 |
| 7.5°  | 10842.6 |
| 10°   | 10930.9 |
| 12.5° | 10909.6 |
| 15°   | 10739.0 |
| 17.5° | 10321.9 |
| 20°   | 9618.6  |
| 22.5° | 8790.4  |
| 25°   | 7904.3  |
| 27.5° | 6904.1  |
| 30°   | 5782.1  |
| 32.5° | 4765.1  |
| 35°   | 3863.9  |
| 37.5° | 2973.3  |
| 40°   | 2132.9  |
| 42.5° | 1393.0  |
| 45°   | 799.3   |
| 47.5° | 423.2   |
| 50°   | 263.4   |
| 52.5° | 182.7   |
| 55°   | 130.9   |
| 57.5° | 94.4    |
| 60°   | 65.5    |
| 62.5° | 42.6    |
| 65°   | 30.4    |
| 67.5° | 27.4    |
| 70°   | 25.9    |
| 72.5° | 19.8    |
| 75°   | 15.2    |
| 77.5° | 13.7    |
| 80°   | 10.7    |
| 82.5° | 7.6     |
| 85°   | 4.6     |
| 87.5° | 3.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

## Scaled Data Report







— 0°-180°







(END OF REPORT)