

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774104

Luminaire Tested: LD6D95BD010-EU6DR2570959027-6LBCSSQMB

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P774104  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D95BD010-EU6DR2570959027-6LBCSSQMB  
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8919.2 lumens  
Efficiency: N/A  
Efficacy: 89.9 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P774104

CATALOG NUMBER: LD6D95BD010-EU6DR2570959027-6LBCSSQMB

### Luminous Intensity Polar Plot



TEST NUMBER: P774104

CATALOG NUMBER: LD6D95BD010-EU6DR2570959027-6LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 |  | 106 | 105 | 104 |  |  | 103 | 102 | 101 |  |  | 99  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 |  | 102 | 100 | 98  |  |  | 99  | 97  | 96  |  |  | 97  |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  |  | 98  | 95  | 93  |  |  | 96  | 93  | 91  |  |  | 94  |
| 4   | 103 | 97  | 93  | 90  | 102 | 96  | 93  | 90  |  | 94  | 91  | 89  |  |  | 93  | 90  | 88  |  |  | 91  |
| 5   | 100 | 93  | 89  | 86  | 98  | 93  | 89  | 86  |  | 91  | 87  | 85  |  |  | 89  | 86  | 84  |  |  | 88  |
| 6   | 97  | 90  | 85  | 82  | 95  | 89  | 85  | 82  |  | 88  | 84  | 81  |  |  | 87  | 83  | 81  |  |  | 85  |
| 7   | 93  | 87  | 82  | 79  | 92  | 86  | 82  | 79  |  | 85  | 81  | 78  |  |  | 84  | 80  | 78  |  |  | 83  |
| 8   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  |  | 82  | 78  | 76  |  |  | 81  | 78  | 75  |  |  | 80  |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  |  | 80  | 76  | 73  |  |  | 79  | 75  | 73  |  |  | 78  |
| 10  | 85  | 78  | 74  | 71  | 85  | 78  | 74  | 71  |  | 77  | 73  | 71  |  |  | 76  | 73  | 71  |  |  | 76  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 3696117 |
| 5°  | 3442467 |
| 10° | 2455607 |
| 15° | 1446255 |
| 20° | 899882  |
| 25° | 493857  |
| 30° | 225858  |
| 35° | 85538   |
| 40° | 38738   |
| 45° | 23286   |
| 50° | 9672    |
| 55° | 6229    |
| 60° | 4349    |
| 65° | 2947    |
| 70° | 447     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23286 cd/sqm



TEST NUMBER: P774104

CATALOG NUMBER: LD6D95BD010-EU6DR2570959027-6LBCSSQMB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 2697.5 | 30.2      |
| 10°-20°   | 3653.5 | 41.0      |
| 20°-30°   | 1933.4 | 21.7      |
| 30°-40°   | 477.3  | 5.4       |
| 40°-50°   | 116.4  | 1.3       |
| 50°-60°   | 30.6   | 0.3       |
| 60°-70°   | 10.3   | 0.1       |
| 70°-80°   | 0.2    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 8284.4 | 92.9      |
| 0°-40°    | 8761.6 | 98.2      |
| 0°-60°    | 8908.7 | 99.9      |
| 0°-90°    | 8919.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 8919.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 33828 |      |
| 5°  | 31387 | ###  |
| 15° | 12786 | 3654 |
| 25° | 4096  | 1933 |
| 35° | 641   | 477  |
| 45° | 151   | 116  |
| 55° | 33    | 31   |
| 65° | 11    | 10   |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P774104

CATALOG NUMBER: LD6D95BD010-EU6DR2570959027-6LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 33828.4 |
| 2.5°  | 33272.5 |
| 5°    | 31387.0 |
| 7.5°  | 27599.1 |
| 10°   | 22133.3 |
| 12.5° | 16731.5 |
| 15°   | 12785.7 |
| 17.5° | 9964.7  |
| 20°   | 7739.4  |
| 22.5° | 5804.2  |
| 25°   | 4096.5  |
| 27.5° | 2747.1  |
| 30°   | 1790.2  |
| 32.5° | 1089.2  |
| 35°   | 641.3   |
| 37.5° | 392.4   |
| 40°   | 271.6   |
| 42.5° | 207.6   |
| 45°   | 150.7   |
| 47.5° | 91.0    |
| 50°   | 56.9    |
| 52.5° | 41.2    |
| 55°   | 32.7    |
| 57.5° | 25.6    |
| 60°   | 19.9    |
| 62.5° | 15.6    |
| 65°   | 11.4    |
| 67.5° | 4.3     |
| 70°   | 1.4     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)