

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774807

Luminaire Tested: LD6D95BD010-EU6DR7070959027-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR7070959027-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10774.6 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774807

CATALOG NUMBER: LD6D95BD010-EU6DR7070959027-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P774807

CATALOG NUMBER: LD6D95BD010-EU6DR7070959027-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105	111	108	106	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94	105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84	99	92	87	83		90	85	82		87	84	81		85	82	79
4	95	87	81	76	93	86	80	76		83	78	75		81	77	74		79	76	73
5	89	80	74	69	88	79	73	69		78	72	68		76	71	68		74	70	67
6	84	75	68	63	83	74	68	63		72	67	63		71	66	62		69	65	62
7	80	69	63	58	78	69	62	58		67	62	58		66	61	57		65	61	57
8	75	65	58	54	74	64	58	54		63	57	53		62	57	53		61	56	53
9	71	61	54	50	70	60	54	50		59	53	50		58	53	49		57	53	49
10	67	57	50	46	66	56	50	46		55	50	46		55	50	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	929175
5°	926857
10°	924848
15°	924591
20°	915556
25°	860046
30°	766733
35°	611320
40°	405924
45°	242686
50°	125819
55°	66119
60°	23382
65°	388
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 242686 cd/sqm



TEST NUMBER: P774807

CATALOG NUMBER: LD6D95BD010-EU6DR7070959027-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	803.7	7.5
10°-20°	2304.9	21.4
20°-30°	3251.6	30.2
30°-40°	2807.0	26.1
40°-50°	1257.0	11.7
50°-60°	329.1	3.1
60°-70°	21.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6360.1	59.0
0°-40°	9167.1	85.1
0°-60°	10753.2	99.8
0°-90°	10774.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10774.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8504	
5°	8451	804
15°	8174	2305
25°	7134	3252
35°	4583	2807
45°	1571	1257
55°	347	329
65°	2	21
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774807

CATALOG NUMBER: LD6D95BD010-EU6DR7070959027-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	8504.2
2.5°	8495.1
5°	8450.7
7.5°	8414.0
10°	8336.0
12.5°	8265.7
15°	8173.9
17.5°	8068.4
20°	7874.2
22.5°	7554.6
25°	7134.0
27.5°	6646.2
30°	6077.3
32.5°	5381.5
35°	4583.2
37.5°	3702.4
40°	2846.0
42.5°	2162.4
45°	1570.6
47.5°	1082.7
50°	740.2
52.5°	510.8
55°	347.1
57.5°	209.5
60°	107.0
62.5°	33.6
65°	1.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)